

NextGen Laserscan By AWTALtd.





Copyright

Unless otherwise stated, the copyright and any other rights in respect of the content of all pages in this booklet, including all texts and images, are owned by AWTA Ltd.

Disclaimer

The information provided in this booklet is for reference only. Although extreme care has been taken to ensure that the information provided is accurate in all respects. You are encourage to conduct your own enquires to verify any particular piece of information provided in this booklet. Actual product may change at the time of build without notice.

The NextGen Laserscan

The measurement of wool fibre diameter can be conducted through four distinct methods as delineated by the International Wool Textile Organisation (IWTO). AWTA Ltd employs the IWTO-12 Laserscan fibre diameter analyser method for fibre diameter certification and fleece measurement services.

In 1972, CSIRO initiated the development of the first Laserscan, establishing the foundation and obtaining approval for the method from the IWTO. Subsequently, in 1996, AWTA Ltd acquired the rights to manufacture and sell the Laserscan and continued its further development.

Introduced in 2014, the NextGen Laserscan has swiftly established itself as a cutting-edge technology in the field. Its global clientele spans a diverse range of end users, encompassing universities, mills, government facilities, and more. The market reception of the NextGen Laserscan has been exceptional, attesting to its innovative features and precision in measuring wool fiber diameter. With its widespread adoption, it has become an indispensable tool for various industries and research institutions, setting new standards in fiber measurement and analysis.



Please scan the QR
code with your phone,
or visit our website.




How does it work?

The Wool Industry has chosen to characterise Fibre Diameter in relation to the average thickness or width of a two-dimensional projected image composed of numerous fibre snippets. In the accompanying figure¹, microscopic fibre cross-sections are depicted. The non-uniform geometry complicates the definition of Mean Fibre Diameter (MFD), rendering it a more intricate task than it may initially appear.

The fibre snippets are very short pieces of fibre, typically around 2mm long, which have been cut at random positions along the length of the fibre. The precise mechanism for doing this usually involves using a Minicore.

The NextGen Laserscan works by mixing fibre snippets with water and a neutral detergent called transportation fluid. The mixture then flows through a measurement cell, where the shadow cast by the wool fibre snippet in a laser beam is utilised to determine its diameter.



¹ Photograph provided by Peter Turner, CISRO Division of Wool Technology, Belmont, Victoria, Australia



Laserscan

Model: NextGen

Technical Information

The AWTA NextGen Laserscan instrument meets the test standards of the International Wool Textile Organisation standard IWTO-12-2012.

The NextGen Laserscan Model is a cutting edge solution that revolutionises precision measurements with its advanced features and user-friendly design. It boasts seamlessly integrated electronics, ensuring optimal performance and reliability. Navigating through intricate measurements is a breeze with the simple and easy-to-use user interface, thanks to Laserscan AWIN II software, empowering users of all skill levels. The temperature-controlled cabinet guarantees stable operating conditions, enhancing the

accuracy and consistency of your results. Embrace efficiency with the full automatic process, streamlining your workflow and minimising manual intervention. The NextGen Laserscan goes beyond conventional standards by employing a water-based transportation fluid, not only promoting environmental sustainability but also contributing to a clean and efficient operation.

Technical Specifications

Power	
Input Voltage	AC 85-264 V (50/60Hz)
Rating	250 W (unit only)
PC & Software	
Hardware	Intel Core i5 or above 8GB RAM 512GB Storage 1080p Display
OS & Software	Windows 8 or 10 Laserscan AWIN II
Dimensions and Weight	
Dimensions (WxDxH)	550mm x 631mm x 911mm
Weight (gross)	160 kg
Environmental Parameters	
Operating Temperature	17°C to 23°C
Operating Humidity	20% to 80%
Accessories (Optional)	
Detergent	Teric 168
Top Sample Preparation	Guillotine
Core Sample Preparation	Minicore
Core Sample Preparation	Snippet Dryer
Manufacturer Warranty	1 Year



Contact:

AWTA Ltd

Engineering Department

24 Robertson St. Kensington

VIC 3031 Australia

Phone: (+61) (03) 9371 2100

Email: manufacturing@awta.com.au

Web page: www.awta.com.au